POLYPROPYLENE FOAM BLOCK BROOMS



SPECTRUM®OMNI SWEEP >>>





Brush made of polypropylene bristles and block with a 3/4" threaded hole to fix the cane.

The fibers have an angled cut for fast and effective sweeping on all types of surfaces. Short, stiff fibers at the front sweep up heavy debris. Long, fine/medium fibers on the back sweep up dust and fine particles.

PIECE			PACK			PALLET			20 FT CONTAINER		48 FT CONTAINER		53 FT CONTAINER		
CODE	SIZE	MEASUREMENTS HEIGHT X WIDTH X LENGTH	APPROX. WEIGHT	MEASUREMENTS HEIGHT X WIDTH X LENGTH	CASE QTY.	WEIGHT	CASES	WEIGHT	PIECES	CASES	PIECES	CASES	PIECES	CASES	PIECES
4188000	18"	3.50 x 2.63 x 18 in	1.71 lb	19.50 x 12.00 x 14.00 in	12	10.50 lb	-	-	-	-	-	-	-	-	-
4188100	24"	3.50 x 2.63 x 24.00 in	2.17 lb	25.90 x 12.50 x 14.00 in	12	26.00 lb	-	-	-	-	-	-	-	-	-

GENERAL SPECIFICATIONS													
SUNLIGHT RESISTANCE		ABRASION RESISTANCE		WATER AB	SORPTION	STIFF	NESS	ELASTIC RECOVERY					
BLOCK	FIBER	BLOCK	FIBER	BLOCK	FIBER	BLOCK	FIBER	BLOCK	FIBER				
G	G	G	G	D	D	G	G	D	D				

THERMAL RESISTANCE*				CHEMICAL AND MOISTURE RESISTANCE											
DISTORTION		SOFTENING		MOISTURE		DILUTED ACID		CONCENTRATED ACID		DILUTED ALKALI		ALCOHOL AND VEGETABLE OILS		PETROLEUM DISTILLATES	
BLOCK	FIBER	BLOCK	FIBER	BLOCK	FIBER	BLOCK	FIBER	BLOCK	FIBER	BLOCK	FIBER	BLOCK	FIBER	BLOCK	FIBER
176 °F	176 °F	266 °F	266 °F	Е	Е	Е	Е	Е	Е	Е	Е	Е	Е	Α	Α

SUGGESTED APPLICATION:

Recommended for fast and effective sweeping on all types of surfaces.

CONTRAINDICATIONS:

DNA

SUPPLEMENTARY PRODUCTS:

This brush can be used with any cane in our line.







E EXCELLENT

G GOOD

A ADEQUATE (1)

D DEFICIENT

DNA DOES NOT APPLY

[CFS BRANDS]



The information provided on this document is for illustrative purposes and may change without notice.